
JASSON DEPENDENCE HYDROTHERAPY 8328 MacArthur Dr. • North Little Rock, AR 72118 501.771.4477 • Fax: 501.771.2333 Customer Service: 800.255.5766 www.jasoninternational.com

Floor Loading / sq.ft :

Carton Weight.:

Cube:

Integrity® Collection Specifications K3260 MicroSilk®



	[39cm] To Drain				
Patents received or pending.					Note: Dimensional Tolerances: ±1/4"
			Air Switch Control	\bigcirc	Includes a quiet, 120V MicroSilk® System, an air switch, On/Off Control and 1 MicroSilk® Delivery Port. Requires (1) 20A, 120v GFCI protected circuit.
Drop-in-Hole Size: Operating Capacity: Overflow Capacity:		30" x 58" 39 Gal. 62 Gal.			Construction: Reinforced Acrylic shell mounted on Level Form [™] pre-leveled full support base.

54.6 lbs.

107 lbs.

28.1 ft.³

We provide products listed with Intertek ETL SEMKO (Edison Testing Laboratories) U.S. and Canadian and with International Association of Plumbing and Mechanical Officials (IAPMO). Consult factory with your listing requirements.